


\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED  
\*未畫倒角者去毛邊

PRELOAD(kgf)	
R.D	
S.F (kgf)	
DRAG TORQUE(kgf-cm)	
LUBRICATION	OIL
DIRECTION OF TURN	R.H
PC DIA.	32.4
BALL DIA.	3.175
BALL TRACK FORM	GOTHIC
BACKLASH	
CIRCUIT	2.5*2
LEAD ANGLE	2.81°
DYNAMIC (kgf)	
STATIC (kgf)	
LEAD	5

SPEC: R32-5B2-RSB



UNCHEAMFERED USE <input type="checkbox"/> C0.5 <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C	CUSTR	DATE	07.08.'98
ROUNDED USE <input type="checkbox"/> M/C <input type="checkbox"/> GRD <input type="checkbox"/> W	SCALE	DWG	林慶銘
UNTOL DIMN mm	TITLE	CHK	
UP 6 30 120 300 600 1200 1800 2400	MATERIAL	APPD	
TO ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5	DWG.NO.	PROCESS NO.	F
THREAD BALL TRACK	THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE	HIWIN® BALLSCREWS	

DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.