


*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*尖銳倒角請去毛邊

PRELOAD(kgf)	_____
R.D	28.392
S.F (kgf)	_____
DRAG TORQUE(Nf-m)	_____
LUBRICATION	_____
DIRECTION OF TURN	RIGHT
PC DIA.	33.26
BALL DIA.	4.763
BALL TRACK FORM	GOTHIC
BACKLASH	_____
CIRCUT	_____
LEAD ANGLE	17.03°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD/PITCH	32/8

SPBC: 4R32-32-4500-4500-0.05

CUSTOMER DRAWING NO.	_____
MC TYPE	_____
ANAL TYPE	_____



UNCHAMFERED USE	<input type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C	CUSTR	HIWIN STD.	DATE	07.24.98
ROUGH MCFIN M/C	GRD	SCALE	1: X	TITLE	BALL SCREW	DWG	蘇興兆
UNTOL DIMN mm	1200 1600	MATERIAL	CF53	CHK	APPD	DWG.NO.	A109NFA2
UP 16 30 120 300 600 1200 2400 2400	±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±1.0 ±1.5	THREAD BALL TRACK	HRC 56 ~ 62	THREAD DIA ALLOWS ABOVE LENGTH	OUT OF HARDNESS TOLERANCE	PROCESS NO.	E

07.24.98	MOD. A	
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS