



Specifications	
	635lb
	22m/min
	2,500 kg
	2:1
	Single
	200mm
	2x10mm, 3x6mm 6x5mm
Speeds	22
	230V

<i>BREAK SHARP EDGES UNLESS OTHERWISE SPECIFIED</i>				DATE	NAME
ROUGH M/C	FIT M/C	GRD	MATERIAL	DRAWN	07/22/09
6.3 a ▽	1.6 a ▽▽	0.4 a ▽▽▽	FINISH	CHECKED	
				ENG APPR.	
				MEG APPR.	

**HIWIN**  
TITLE: \_\_\_\_\_