


*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未畫圓角者皆去毛刺

PRELOAD (kgf)	—
R.D	16.924
S.F (kgf)	—
DRAG TORQUE (kgf-cm)	—
LUBRICATION	—
DIRECTION OF TURN	RIGHT
PC DIA.	20.2
BALL DIA.	3.175
BALL TRACK FORM	GOTHIC
BACKLASH	—
CIRCUIT	—
LEAD ANGLE	4.51°
DYNAMIC (kgf)	—
STATIC (kgf)	—
LEAD	5

SPEC: R20-5-3000-3000-0.05

CUSTOMER DRAWING NO.	
MC TYPE	
ANA. TYPE	



UNCHAMFERED USE	□	CO.5	■	C1	□	CG	CUSTR	HIWIN STD.	DATE
ROUNDED USE	□	CO.5	■	C1	□	CG	SCALE	HIWIN STD.	DATE
SCALE	1: X		TITLE		BALL SCREW		CHK		APPD
UP		6	30	120	300	600	1200	TOVER	MATAL
DIP		±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5
DIM. NO.		DIM. mm		DIM. NO.		DIM. mm		DIM. NO.	
THREAD BALL TRACK		HRC 56 ~ 62		THREAD END ALLOWS ABOVE LENGTH		OUT OF HARDNESS TOLERANCE		HIWIN® BALLSCREWS	

CUSTOMER DRAWING NO.		DATE	07.08.'98
MC TYPE		DWG	趙唯亮
ANA. TYPE		CHK	
		APPD	
		PROCESS NO.	I.E

1	2	3	4	5	6	7	8	9
A								
B								
C								
D								
E								
F								
G								

DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.