



M50X2P
 MD50_{-0.038}
 -0.318
 PD48.701_{-0.038}
 -0.218

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
 *未量例角者去毛邊

PRELOAD(kgf)	
R. D	
S. F (kgf)	
DRAG TORQUE(Ng-cm)	
LUBRICATION	OIL
DIRECTION OF TURN	R. H
P.C. DIA.	32.4
BALL DIA.	3.175
BALL TRACK FORM	GOTHIC
BACKLASH	0.05MAX
CIRCUIT	2.5*2
LEAD ANGLE	2.81°
DYNAMIC (kgf)	
STATIC (kgf)	
LEAD	5.

SPEC: R32-5B2-RSB

UNCHAMFERED USE <input type="checkbox"/> CO.5 <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C2 BOX/ W.C./ P.N. W./ C1 G.R.F. 0.4g 0.2g 6.5g 0.2g 6.5g 0.2g	SCALE 1: X CUSTR HIWIN STD. DATE C7.08.'98	TITLE BALL SCREW DWG 林登銘 CHK APPD
CUSTOMER DRAWING NO. MC TYPE ANAL TYPE	T: e300 E: e:	THREAD LENGTH UP TO 6 30 120 300 600 1200 2400 2400 ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5 UN TOL DIMM mm 300 600 1200 OVER 600 1200 2400 2400 THREAD BALL TRACK HRC 58 ~ 62
THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE		HIWIN® BALLSCREWS

DATE	MODIFICATION	APPROVED
------	--------------	----------

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.