


*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未量視角者去毛邊

PRELOAD (+gr)	_____
R.D	29.124
S.F (kgf)	_____
DRAG TORQUE (gf-cm)	_____
LUBRICATION	_____
DIRECTION OF TURN	RIGHT
PC DIA.	32.4
BALL DIA.	3.175
BALL TRACK FORM	GOTHIC
BACKLASH	_____
CIRCUIT	_____
LEAD ANGLE	2.81°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	5.

SPEC: R32-5- Δ 4500- Δ 4500-0.05

CUSTOMER DRAWING NO.	_____
MC TYPE	_____
MAN. TYPE	_____



UNCHAMFERED USE	<input type="checkbox"/> CO.5	<input type="checkbox"/> C1	<input type="checkbox"/> C
SCALE	1: X		
UNIT	mm		
UP	6	30	120
TD	6	30	120
±0.1	±0.2	±0.3	±0.4
±0.5	±0.8	±1.0	±1.5

CUSTOMER TITLE	HIWIN STD. BALL SCREW
MATERIAL	CF53
UNGC NO.	A109PEA2
PROCESS NO.	_____

DATE	07.24.'98
DWG	蕭興光
CHK	_____
APPD	_____

07.24.'98	MOD. A	_____
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS