

1  
A10RBPA1

2  
Released by HIWIN design group.

3  
4  
6  
G  
▽ (▽▽)

A

B



C

D

E

F

G



PRELOAD(kgf)	~
R.D	21.974
S.F (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	26.03

SPEC: 2R25-25A2-DRSB

MAX. AXIAL LOAD(kgf)	LUBRCATION	BALL DIA.	3.969
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	~
DN VALUE	EI TYPE ASSEMBLY METHOD	CIRCUIT	1.5*2
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	17
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)	~
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	~
		LEAD / PITCH	25/12.5

<p>E300: ~</p>	UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R SCALE 1: X MENTAL SH: Rolled DATE 2003.12.12 NT: SNCM220 DWG 巫蘭馨 THREAD BALL TRACK APPD HRC 58 ~ 62 PROCESS NO. G CUSTR DWG.NO. A10RBPA1
----------------	---

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未畫倒角者以R0.5MAX

● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

DATE	MODIFICATION	APPROVED
------	--------------	----------

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS