



A11456A2

Released by HIWIN design group.

∇∇ (∇∇)



DYNAMIC BEARING(kgf)	5755
STATIC BEARING(kgf)	6653
PRELOAD(kgf)	~
R.D	~
S.F (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	36.275

SPEC: 4R36-36S2-DFSHR1

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA.	4.763
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	~
DN VALUE	EI TYPE ASSEMBLY METHOD	CIRCUIT	1.8*2
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	17.53
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)	~
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	~
		LEAD/PITCH	36/18

THAMFERED USE	<input type="checkbox"/> R0.5	<input checked="" type="checkbox"/> R1	<input type="checkbox"/> R	MATERIAL	SH: ROLLED	DATE	2008.06.09
ROUGH WZ/FIN W/C	<input type="checkbox"/> 25°	<input type="checkbox"/> 6.35°	<input type="checkbox"/> 0.25°	SCALE	NT: SNCM220/SCM415	DWG	Sigma
UNTOL DIMN mm	UP 6 16 30 120 300 600 1200 2400 2400	TO 6 30 120 300 600 1200 2400 2400	GRD	SCALE	THREAD BALL TRACK	APPD	Michelle
	±0.1	±0.2	±0.3	±0.4	HRC 56 ~ 62	PROCESS NO.	G
						CUSTR	
						DWG.NO.	A11456A2

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未畫倒角者以R0.5MAX  
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2008.06.09	MOD. Δ ~ Δ	Michelle
DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.