



A10JKBA1

A
B
C
D
E
F
G





M17x1P
MD17^{-0.026}_{-0.206}
PD16.35^{-0.026}_{-0.144}

- 1. MAX AXIAL LOAD: _____ kgf
- 2. MAX BALLSCREW ROTATIONAL SPEED: _____ rpm
- DN VALUE: _____
- ACCELERATION= _____ m/sec²
- 3. MAX FEED RATE: _____ m/min

PRELOAD(kgf)	_____
R.D	_____
S.F (kgf)	_____
DRAG TORQUE(kgf-cm)	_____
LUBRICATION	_____
DIRECTION OF TURN	R.H
PC DIA.	10.2
BALL DIA.	2
BACKLASH	_____
CIRCUIT	2
LEAD ANGLE	4.46°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	2.5

SPEC:R10-2.5T2-RS1



UNCHAMFERED USE	<input checked="" type="checkbox"/> R0.5	<input type="checkbox"/> R1	<input type="checkbox"/> R
ROUGH W/CI	<input type="checkbox"/> 25°	<input type="checkbox"/> 6.3°	<input type="checkbox"/> 0.4°
GRD	<input type="checkbox"/> 25°	<input type="checkbox"/> 6.3°	<input type="checkbox"/> 0.4°
SCALE	1: X		
UNTOL DIMN mm			
UP	6	30	120
DOWN	6	30	120
OVER	120	300	600
OVER	1200	2400	2400
T	±0.1	±0.2	±0.3
E	±0.4	±0.5	±0.8
OVER	±1.0	±1.5	±1.5

MATAL	NT: SNCM220	DATE	11.07.'01
THREAD BALL TRACK	HRC 58 ~ 62	DWG	鄒健偉
CUSTR		APPD	
DWG.NO.	A10JKBA1	PROCESS NO	G E

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED	CUSTOMER DRAWING NO.
*未畫倒角者以R0.5MAX	
⊙ THREAD END ALLOWS ABOVE LENGTH	MC TYPE
⊙ OUT OF HARDNESS TOLERANCE	AXIAL TYP

DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS