



A114 AIA3

Released by HIWIN design group.

∇∇ (∇∇∇)



PRELOAD (kgf)	~
R.D	~
S.F (kgf)	~
DYNAMIC TORQUE (N-m)	~
DIRECTION OF TURN	R
PC DIA	41.85
MAX. AXIAL LOAD (kgf)	6.35
MAX. ROTATIONAL SPEED (rpm)	~
DN VALUE	4
MAX. FEED RATE (m/min)	4.35
ACCELERATION (m/sec ²)	3396
SUPPORT METHOD	AB489
LEAD	10

SPEC: R40-10T4-FSI


MAX. AXIAL LOAD (kgf)	LUBRICATION	SPACE BALL	BACKLASH
MAX. ROTATIONAL SPEED (rpm)	EI TYPE ASSEMBLY METHOD	CIRCUIT	LEAD ANGLE
DN VALUE	CUSTOMER DRAWING NO.	DYNAMIC (kgf)	STATIC (kgf)
MAX. FEED RATE (m/min)	CUSTOMER MC TYPE	AB489	LEAD
ACCELERATION (m/sec ²)	CUSTOMER AXIAL TYPE		
SUPPORT METHOD			

UNCHAMFERED USE	RO 5	HR	DATE	2007.05.25
SCALE	1:X	MATERIAL	DATE	2007.05.25
THREAD BALL TRACK (APPROX)	LADY	DATE	DATE	2007.05.25
HRC	56 ~ 62	PROCESS NO.		G
CUSTOMER		DWG. NO.		A114 AIA3

05.25.07	MOD.	△-△	Lady
DATE	MODIFICATION	APPROVED	

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

⊙ BREAK SWAMP CODE UNLESS OTHER SPECIFIED
*??????RO.5MAX
⊙ THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE



HIWIN BALLSCREWS