



A
B
C
D
E
F
G



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	33.26
BALL DIA.	4.763

SPEC: 4R32-32A2-DRSB

MAX. AXIAL LOAD(kgf)		LUBRICATION		BALL DIA.	4.763
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH Δ	
DN VALUE		EI TYPE ASSEMBLY METHOD		CIRCUIT	1.5*2
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	17.03
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		Δ DYNAMIC (kgf)	1681
SUPPORT METHOD		CUSTOMER AXIAL TYPE		Δ STATIC (kgf)	4208
				LEAD/PITCH	32/8



UNCAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R	SCALE
ROUGH M/C FIN. M/C GRD.	1: X
25° 6.3φ 0.2φ	
NORMAL TOLERANCE mm	
UP 16 30 120 300 600 1200 OVER	
±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5	

MAT. SH: ROLLED	DATE	2008.05.16
NT: SNCM220/Equivalent	DWG	Penny
THREAD BALL TRACK	APPD	Michelle
HRC 56 ~ 62	PROCESS NO.	G
CUSTR		
DWG.NO.	A10WXP2	

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未畫倒角者以R0.5MAX
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2008.05.16	MOD. Δ~Δ	Michelle
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS