



A114ANB2

Released by HIWIN design group.

∇∇ (∇∇∇)

A
B
C
D
E
F
G

05.25.07	MOD.	△	△	Lady
DATE	MODIFICATION			APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

◎ BREAK SWAMP CODE UNLESS OTHER SPECIFIED
*??????R0.5MAX
◎ THREAD END ALLOWS ABOVE LENGTH
OUT OF HARDNESS TOLERANCE

SPEC: R40-ST4-FSI

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA	3.175
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	~
DN VALUE	FI TYPE ASSEMBLY METHOD	CIRCUIT	4
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	2.28
ACCELERATION (m/sec ²)	CUSTOMER MC TYPE	DYNAMIC (kgf)	Δ1414
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	Δ4621
		LEAD	5

UNCHAMFERED USE	<input type="checkbox"/> R0.5	<input type="checkbox"/> R1	<input type="checkbox"/> R	DATE	2007.05.25
SCALE	1:X	MATERIAL	SH: ROLLED	DATE	2007.05.25
UNIT	mm	THREAD	NT-SNM220/SCM415	DWG	KAI
PRECISION	±0.1	THREAD BALL TRACK	APPD	Lady	
		HRC	56 ~ 62	PROCESS NO.	G
		CUSTOMER			
		DWG. NO.	A114ANB2		

E300: ~

HIWIN BALLSCREWS