



NOTE: 1. Steel ball tolerance must be in the range of -0.0025, -0.015  
2. DIN 69051 part 5 form B TYPE 1.

PRELOAD(kgf)	_____
R.D	_____
S.F (kgf)	_____
DRAG TORQUE(kgf-cm)	_____
DIRECTION OF TURN	R.H
PC DIA.	34.26
BALL DIA.	6.35
BACKLASH	0.03MAX
CIRCUIT	4
LEAD ANGLE	5.31°
DYNAMIC (kgf)	2900
STATIC (kgf)	6404
LEAD	10

SPEC: R32-10T4-FSI

MAX. AXIAL LOAD(kgf)	LUBRICATION		BALL DIA.	6.35
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL		BACKLASH	0.03MAX
DN VALUE	EI TYPE ASSEMBLY METHOD		CIRCUIT	4
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.		LEAD ANGLE	5.31°
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE		DYNAMIC (kgf)	2900
SUPPORT METHOD	CUSTOMER AXIAL TYPE		STATIC (kgf)	6404
			LEAD	10

 E300: _____	UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R	MATA SH: ROLLED DATE 2007.07.17
	SCALE 1: X	DATE JANET
UNTOL DIMN mm UP 6 30 120 300 600 1200 2400 TO 6 30 120 300 600 1200 2400	THREAD BALL TRACK APPD MICHELLE	DWG NO. A1158TA1
CUSTR H-CIHCAGO		

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未畫倒角者以R0.5MAX  
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

