


1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9

A  
B  
C  
D  
E  
F  
G




\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED  
\*未畫倒角者去毛邊

PRELOAD(kgf)	---
R.D	16.924
S.F (kgf)	---
DRAG TORQUE(kgf-cm)	---
LUBRICATION	---
DIRECTION OF TURN	RIGHT
PC DIA.	20.2
BALL DIA.	3.175
BALL TRACK FORM	GOthic
BACKLASH	---
CIRCUIT	---
LEAD ANGLE	4.58°
DYNAMIC (kgf)	---
STATIC (kgf)	---
LEAD	5.08

SPEC: R20-5.08-3000-3000-0.05

CUSTOMER DRAWING NO.	
MC TYPE	
ANAL TYPE	



UNCAMFERED USE <input type="checkbox"/> C0.5 <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C	SCALE	CUSTR	HIWIN STD.	DATE
ROUGH M/C FIN. M/C <input type="checkbox"/> GRD <input type="checkbox"/>	1: X	TITLE	DWG	12.17.'98
UNTOL DIMN mm		MATAL	CHK	
UP 6 30 120 300 600 1200 2400 2400		DWG.NO.	APPD	
±0.1   ±0.2   ±0.3   ±0.4   ±0.5   ±0.6   ±1.0   ±1.5				
THREAD BALL TRACK				
HRC 56 ~ 62				
⊕ THREAD END ALLOWS ABOVE LENGTH				
OUT OF HARDNESS TOLERANCE				

DATE	12.17.'98
DWG	吳秋燕
CHK	
APPD	
PROCESS NO.	E
HIWIN® BALL SCREWS	

DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.