


1
A10LN4A1

2
Released by HIWIN design group.

3
▽ (▽▽)

4
5
6
7
8
9
4500



PRELOAD(kgf)	~
R.D.	27.77
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	34.26
BALL DIA.	6.35
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	5.31
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	10

SPEC: R32-10-4500-4500-0.05

MAX. AXIAL LOAD (kgf)		LUBRICATION	
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL	
DN VALUE		ET TYPE ASSEMBLY METHOD	
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.	
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE	
SUPPORT METHOD		CUSTOMER AXIAL TYPE	

THREAD LENGTH 	UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R ROUGH W/ FIN. M/C 1 <input type="checkbox"/> GRIND <input type="checkbox"/> 0.45 250p 5-30p 0.45p	SCALE 1: X NORMAL TOLERANCE mm UP 6 150 20 300 600 1200 2400 OVER TO ±1.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5	MAT. SH: CF53/Equivalent DATE 2/08/09.15 DWG Michelle
*BREAK SHARP EDGE UNLESS OTHER SPECIFIED *未磨倒均者以R0.5MAX * THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE	φ300p: 0.05 ep: 0.75	HIWIN BALLSCREWS	THREAD BALL TRACK HRC 56 ~ 62 APPD SIGMA PROCESS NO. G
DATE MODIFICATION APPROVED	* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.	CUSTR HIWIN STD. DWG.NO. A10LN4A1	DATE 2/08/09.15 DWG Michelle APPD SIGMA PROCESS NO. G

DATE	MODIFICATION	APPROVED
------	--------------	----------