

A10GBLA1

A  
B  
C  
D  
E  
F  
G

4500

15



15



∅25

- 1. MAX AXIAL LOAD: \_\_\_\_\_ kgf
- 2. MAX ROTATIONAL SPEED: \_\_\_\_\_ rpm  
DN VALUE: \_\_\_\_\_
- 3. MAX FEED RATE: \_\_\_\_\_ mm/min

PRELOAD(kgf)	_____
R.D	22.294
S.F (kgf)	_____
DRAG TORQUE(kgf-cm)	_____
LUBRICATION	OIL
DIRECTION OF TURN	R.H
PC DIA.	25.57
BALL DIA.	3.175
BACKLASH	_____
CIRCUIT	_____
LEAD ANGLE	3.56°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	5.

SPEC: R25-5-4500-4500-0.05



UNCHAMFERED USE	<input type="checkbox"/> C0.5	<input checked="" type="checkbox"/> C1	<input type="checkbox"/> C
ROUGH M/FIN	<input type="checkbox"/> M	<input checked="" type="checkbox"/> F	<input type="checkbox"/> G
SCALE	1: X		

UNITOL	DIAM	mm
UP	16	30
TD	120	300
±0.1	±0.2	±0.3
	±0.4	±0.5
	±0.8	±1.0
	±1.5	

WATAL	SH: CF53	DATE	10.26.'00
		DWG	林炳盛
	THREAD BALL TRACK	APPD	林炳盛
	HRC 56~62	PROCESS NO.	E
CUSTR	HIWIN STD.		
DWG.NO.	A10GBLA1		

*BREW SHARP EDGE UNLESS OTHER SPECIFIED	CUSTOMER DRAWING NO.
*未磨倒角者以R0.5MAX	
∅ THREAD END ALLOWS ABOVE LENGTH	MC TYPE
OUT OF HARDNESS TOLERANCE	ANAL TYPE

E 300:0.05

HIWIN® BALLSCREWS

DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.