


A
B
C
D
E
F
G



PRELOAD(kgf)	~
R.D.	29.124
S.F. (kgf)	~
DRAG TORQUE(Nf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	32.4
BALL DIA.	3.175
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	2.86
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	5.08

SPEC: R32-5.08-4000-4000-0.05

MAX. AXIAL LOAD (kgf)	LUBRICATION	
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	
DN. VALUE	EI TYPE ASSEMBLY METHOD	
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	
ACCELERATION (m/sec ²)	CUSTOMER MC TYPE	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	
UNCHAMFERED USE <input type="checkbox"/> CO.S <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C	SCALE	DATE
3000 1200 600 300 150 75 37.5 18.75 9.375 4.6875	1:X	2014.02.07
NORMAL TOLERANCE mm	MAT.	S± CF53/Equivalent
UP 6 30 120 300 600 1200 2400 2400	THREAD BALL TRACK	CHK
±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.6	HRC 56 ~ 62	APPD
V300p: 0.05	CUSTR	HIWIN STD.
ep: 0.067	DWG.NO.	A1128VA1

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未破角均係去毛邊 (CO.2MAX)
● THREAD END ALLows ABOVE LENGTH OUT OF HARDNESS TOLERANCE



DATE	MODIFICATION	APPROVED
------	--------------	----------

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.