


PRELOAD(kgf)	~
R.D.	9.946
S.F. (kgf)	~
DRAG TORQUE(N·m)	~
DIRECTION OF TURN	R
P.C. DIA.	12.01
BALL DIA.	2
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	7.55°
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	5

SPEC:R12-5-1500-1500-0.05

MAX. AXIAL LOAD(kgf)	LUBRICATION	
MAX. ROTATING SPEED (rpm)	SPACE BALL	
DN VALUE	IF TYPE ASSEMBLY METHOD	
MAX. FEED RATE(m/min)	CUSTOMER DRAWING NO.	
ACCELERATION (m/sec ²)	CUSTOMER NC TYPE	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	
UNCHAMFERED USE	<input checked="" type="checkbox"/> R0.5 <input type="checkbox"/> R1 <input type="checkbox"/> R	
ROUNDER RATIO M/C	<input type="checkbox"/> CRD <input type="checkbox"/> SCALP	
	1: X	
NORMAL TOLERANCE mm		
UP	6 30 120 300 600 1200 2400 2400	
±0.1	±0.3 ±0.4 ±0.5 ±0.8 ±1.2 ±1.5	
MAT.	SH:CF53/Equivalent	DATE 2009.04.15
THREAD BALL TRACK	HRC 56 ~ 62	DWG Penny
		PROCESS NO. G



* BREAK SHARP EDGE, UNLESS OTHER SPECIFIED
 * 未畫銳角者均R0.5MAX
 ● THREAD DIA. ADOPTS ABOVE LENGTH
 BUT OF HARDNESS TOLERANCE

HIWIN BALLSCREWS

CUSTR H W N STD
 DWG.NO. A11FXWB1

2009.04.15	A1-B1	Michelle
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.