


*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未畫倒角者去毛邊

PRELOAD(kgf)	151
R.D	29.324
S.F (kgf)	0.37-1.50
DRAG TORQUE(Nf-cm)	1.09-4.38
LUBRICATION	OIL
DIRECTION OF TURN	R.H
PC DIA.	32.6
BALL DIA.	φ3.175
BALL TRACK FORM	GOETHIC
BACKLASH	0
CIRCUIT	2.5*2
LEAD ANGLE	2.84°
DYNAMIC (kgf)	1886
STATIC (kgf)	5666
LEAD	5.08

SPEC: R32-5.08B2-FSV-1546-1800-0.012



CUSTOMER DRAWING NO.	
MC TYPE	
ANAL TYPE	X

UNCHAMFERED USE	<input type="checkbox"/>
CO.5	<input type="checkbox"/>
C1	<input type="checkbox"/>
C3	<input type="checkbox"/>
SCALE	1: X
T: -	0.046 e300; 0.012
E: 0.035	e: 0.025

UNTOL DIMN mm	UP	e	30	120	300	600	1200	1800	2400
ROUGH/MAZ/FIN	M/C1	GRD							
MATERIAL	A108QVAT								
THREAD BALL TRACK	HRC 58 ~ 62								
THREAD END	THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE								

CUSTR	H-USA	DATE	02.18.98'
TITLE	BALL SCREW	DWG	林麗真
SH: 50CrMo4	CHK		
NT: SNCM220	APPD		
PROCESS NO.1	E		

REVISION	DATE	MODIFICATION	APPROVED
1	02.11.98'	A ISSUE 1st REVISION	

2-φ10.5THRU/BCD58.5
D-D VIEW
* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.