



• **LAH2 Specifications**

Model	Screw type	Thrust max. (N)	Holding force max. (N)	Speed (mm/s) Load=Max. / Load=0	Standard stroke(mm):S							Duty cycle %	Max.current (A) 24VDC
					100	150	200	250	300	350	400		
LAH2-1A	ACME	6000	5000	4/6	100	150	200	250	300	350	400	10	6
LAH2-2A	ACME	5000	5000	5/7.5	100	150	200	250	300	350	400	10	6
LAH2-3A	ACME	3000	3000	9/14	100	150	200	250	300	350	400	10	6
LAH2-1B	Ball screw	6000	5000	5/7.5	100	150	200	250	300	350	400	10	6

* Holding force (push direction only)



• **LAH2 Ordering Information**

