


1
A10P55A1

2
Released by HIWIN design group.

3
4
G
∇ (∇∇)

5600




∅40

PRELOAD (kgf)	~
R.D	36.444
S.F (kgf)	~
DRAG TORQUE (kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	40.5
BALL DIA.	3.969
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	2.86
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	6.35

SPEC: R40-6.35-5600-5600-0.05

MAX. AXIAL LOAD(kgf)		LUBRCATION		BALL DIA.	3.969
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	~
DN VALUE		EI TYPE ASSEMBLY METHOD		CIRCUIT	~
MAX. FEED RATE(m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	2.86
ACCELERATION(m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	~
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	~
				LEAD	6.35

UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R		MATERIAL	SH: CF53	DATE	2003.04.09					
ROUGH M/C	FIN M/C	GRD	SCALE	NT: SNCM220	DWG	???				
25 _a	6.3 _a	0.4 _a	1: X	THREAD BALL TRACK	APPD					
UNTOL DIMN mm			HRC 56 ~ 62			PROCESS NO.	G			
UP TO	6	30	120	300	600	1200	2400	2400	CUSTR	HIWIN STD.
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5	DWG.NO.	A10P55A1



*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*??????R0.5MAX
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.

DATE	MODIFICATION	APPROVED
------	--------------	----------

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS