


3000

15



(ø16)


PRELOAD(kgf)	~
R. D.	12.684
S. F. (kgf)	~
DRAG TORQUE(Ngf-m)	~
DIRECTION OF TURN	R
P.C. DIA	15.96
BALL DIA	3.175
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	11.28
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	10

SPBC: R16-10-3000-3000-0.05

MAX. AXIAL LOAD(kgf)	LUBRICATION	
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	
DN VALUE	ET TYPE ASSEMBLY METHOD	
MAX. FEED RATE(m/min)	CUSTOMER DRAWING NO.	
ACCELERATION(m/sec ²)	CUSTOMER MC TYPE	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	
		LEAD 10

UNCHAMFERED USE	<input type="checkbox"/> R0.5	<input checked="" type="checkbox"/> R1	<input type="checkbox"/> R	MAT.	SH: CF53/Equivalent	DATE	2009.12.11
ROUGH/ACFIN M/C	GRD	0.4	0.2	SCALE		DWG	Rita
		0.05	0.02	1: X		THREAD BALL TRACK	APPD
						HRC	56 ~ 62
						CUSTR	HIWIN STD
						DWG.NO.	A10AF1A1

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未磨倒角者以PRO.5 MAX
● THREAD END ALLONS ABOVE LENGTH OUT OF HARDNESS TOLERANCE



UP	6	30	120	300	600	1200	2400
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0

HIWIN® BALLSCREWS

DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.