


A10EE9A1

Released by HIWIN design group.

列印者:00018215 李宜軒 列印時間:2018/09/14 13:53:21 輸出來源:A000004841 doralee

機密級 More Confidential



PRELOAD(kgf)	~
R.D.	6.136
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	8.2
BALL DIA.	2
BACKLASH	~
CIRCUIT	~
LEAD ANGLE	5.54
DYNAMIC (kgf)	~
STATIC (kgf)	~
LEAD	2.5

SPEC:R8-2.5-800-800-0.05

MAX. AXIAL LOAD(kgf)		LUBRICATION		BALL DIA.	2
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	~
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	~
MAX. FEED RATE(m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	5.54
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	~
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	~

<p>UNCHAMFERED USE <input type="checkbox"/> CO.5 <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C</p> <p>ROUGH M/C/FIN M/C/GRD <input type="checkbox"/> 25a <input type="checkbox"/> 6.3a <input type="checkbox"/> 0.4a <input type="checkbox"/> (VV)</p> <p>SCALE 1: X</p> <p>NORMAL TOLERANCE mm</p> <table border="1"> <tr><th>UP TO</th><th>6</th><th>30</th><th>120</th><th>300</th><th>600</th><th>1200</th><th>2400</th><th>OVER 2400</th></tr> <tr><td>±0.1</td><td>±0.2</td><td>±0.3</td><td>±0.4</td><td>±0.5</td><td>±0.8</td><td>±1.0</td><td>±1.5</td><td></td></tr> </table>	UP TO	6	30	120	300	600	1200	2400	OVER 2400	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5		MAT. SH: CF53/Equivalent	DATE 2010.04.02
UP TO	6	30	120	300	600	1200	2400	OVER 2400												
±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5													
<p>THREAD LENGTH</p> <p>He_s</p> <p>ep: 0.133</p>	<p>THREAD BALL TRACK</p> <p>HRC 56 ~ 62</p>	<p>APPD Cody</p> <p>PROCESS NO. G</p>																		
<p>HIWIN® BALLSCREWS</p>	CUSTR HIWIN STD.	DWG.NO. A10EE9A1																		

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未畫倒角者以CO.2MAX

THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2010.04.02	MOD. Δ	Cody
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.