



M17x1P
 MD17^{-0.026}_{-0.206}
 PD16.35^{-0.026}_{-0.144}

NOTE: Steel ball tolerance must be in the range of $-0.0025, -0.010$
 (鋼球公差限用 $-0.0025, -0.010$)

PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
TRAC TORQUE(Ngf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	10.2
BALL DIA.	2
BACKLASH	0.03MAX
CIRCUIT	2
LEAD ANGLE	4.46
DYNAMIC (kgf)	174
STATIC (kgf)	26.3
LEAD	2.5

SPEC:R10-2.5T2-RS1

MAX AXIAL LOAD(kgf)	LUBRICATION	SPACE BALL	BALL DIA.	2
MAX ROTATION SPEED (rpm)	ET TYP. ASSEMBLY METHOD		BACKLASH	0.03MAX
DN VALUE	CUSTOMER DRAWING NO.		CIRCUIT	2
MAX FEED RATE (m/min)	CUSTOMER WC TYPE		LEAD ANGLE	4.46
ACCELERATION (m/sec ²)	CUSTOMER AXIAL TYPE		DYNAMIC (kgf)	174
SUPPORT METHOD			STATIC (kgf)	26.3
			LEAD	2.5

	UNCHAMFERED USE <input checked="" type="checkbox"/> R0.5 <input type="checkbox"/> R1 <input type="checkbox"/> R GROU W/CHIN M/C <input type="checkbox"/> GRD <input type="checkbox"/> S 25° 0.5° 0.4° 0.3°	SCALE 1: X MAT. SH: ROLLED DATE 2008.11.05 NT: SNOM220/Equivalent DWG Penny
	NORMAL TOLERANCE mm 10 16 20 30 40 50 60 80 100 1200 2400 0.01 ±0.2 0.03 0.04 0.05 0.06 0.1 0.15	THRE AD BALL TRACK APPD Michelle HRC 56 ~ 62 PROCESS NO. C

*BREW SHARP EDGE (UNLESS OTHER SPECIFIED)
 *未量倒角者以R0.5MAX
 ● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2008.11.05	MOD. Δ-Δ	Michelle
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

