




A10JSJA1

693.42




F0.4X0.2DIN509

1. MAX AXIAL LOAD: \_\_\_\_\_ kgf
2. MAX BALLSCREW ROTATIONAL SPEED: \_\_\_\_\_ rpm
- DN VALUE: \_\_\_\_\_
- ACCELERATION= \_\_\_\_\_ m/sec<sup>2</sup>
3. MAX FEED RATE: \_\_\_\_\_ m/min

SPEC: L32-5.08B2-FSV-527.56-693.42-0.012

PRELOAD(kgf)	207
R.D	29.324
S.F (kgf)	0.65~1.92
DRAG TORQUE(Ng-m)	1.88~5.64
LUBRICATION	
DIRECTION OF TURN	L.H.
PC DIA.	32.6
BALL DIA.	3.175
BACKLASH	0
CIRCUIT	2.5*2
LEAD ANGLE	2.84°
DYNAMIC (kgf)	1886
STATIC (kgf)	5666
LEAD	5.08



 THREAD LENGTH		UNCHAMFERED USE <input type="checkbox"/> R0.5 <input type="checkbox"/> R1 <input type="checkbox"/> R				MATERIAL SH: 50CrMn4 NT: SNCM220		DATE 11.29.'01 DWG 巫鳳馨	
THRESHOLD TOLERANCE R0.5 6.30 12.50 20.00 31.50 50.00 80.00 125.00 200.00 315.00 500.00 800.00 1250.00 2000.00		UNC TOLER DIMN mm 10. 30 120 300 600 1200 2400 4800		SCALE 1: X THREAD BALL TRACK APPD HRC 58 ~ 62 PROCESS NO G1 E		CUSTR HIWIN STD. DWG.NO. A10JSJA1			

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED. *未畫倒角者以R0.5MAX	CUSTOMER DRAWING NO.
MC TYPE	
ANAL TYPE	
T: -0.016 e300: 0.012	
E: 0.016 e: 0.014	

DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.