



NOTE: 1. Steel ball tolerance must be in the range of $-0.0025, -0.015$.
 2. ∇ : Precision Turning.

SPEC: R40-10T4-RS1

MAX. AXIAL LOAD (kgf)	LUBRICATION	PRELOAD (kgf)	~
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	R.D	~
DN. VALUE	EI TYPE ASSEMBLY METHOD	S.F (kgf)	~
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	DRAG TORQUE (kgf-cm)	~
ACCELERATION (m/sec ²)	CUSTOMER MC TYPE	DIRECTION OF TURN	R
SUPPORT METHOD	CUSTOMER AXIAL TYPE	PC DIA.	41.85
		MAX. DIA.	6.35
		BACKLASH ∇	0.03 MAX
		CIRCUIT	4
		LEAD ANGLE	4.35
		DYNAMIC (kgf)	3396
		STATIC (kgf)	8489
		LEAD	10

UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R	SCALE	MATERIAL	SH: ROLLED	DATE	2007.07.16
ROUGH W/C FIN W/C GRD	SCALE		NT: SNCM220/SCM415	DWG	JANET
UNTOL DIMM mm	1: X		THREAD BALL TRACK	APPD	MICHELLE
UP 16 30 120 300 600 1200 2400			HRC 56 ~ 62	PROCESS NO.	G
±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5			CUSTR	H-CHICAGO	
			DWG.NO.	A114APC5	

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
 *未畫倒角者以R0.5MAX
 ● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2007.07.16	MOD. ∇	MICHELLE
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

