



PRELOAD(kgf)	~
R.D	~
S.F (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	15.96
BALL DIA.	3.175
BACKLASH	△ 0.03MAX
CIRCUIT	3
LEAD ANGLE	11.28
DYNAMIC (kgf)	623
STATIC (kgf)	1102
LEAD	10

SPEC: R16-10T3-FSI

MAX. AXIAL LOAD (kgf)	LUBRICATION	
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	
DIN VALUE	EI TYPE ASSEMBLY METHOD	
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	
ACCELERATION (m/sec ²)	CUSTOMER MC TYPE	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	

THREAD LENGTH 0	UNCHAMFERED USE ROUGH M/CFIN M/C 25α 6.3α 0.4α 0.04α	GRD 25 α α α α	R0.5 R1 R SCALE 1: X	MATAL SH: ROLLED DATE 2007.07.16 INT: SNCM220/SCM415 DWG JANET
	UNTOL DIMN mm UP 6 30 120 300 600 1200 2400 TO 0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5	THREAD BALL TRACK APPD MICHELLE HRC 56 ~ 62 PROCESS NO. G		
CUSTR H-CHICAGO		DWG.NO. A114IHA3		

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
 *未量倒角者以R0.5MAX
 ● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2007.07.16	MOD	
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.