



UNCONTROLLED IF PRINTED

$\sqrt{Ra6.3}$ ($\sqrt{Ra0.4}^G$)



BREAK SHARP EDGES UNLESS OTHERWISE SPECIFIED

PRELOAD(kgf)	~
R.D.	12.969
S.F. (kgf)	~
DRAG TRQ(kgf-cm)	~
TURN DIRECTION	R
P.C. DIA.	16.1
BALL DIA.	3
BACKLASH	0.04 MAX
CIRCUIT	3
LEAD ANGLE	17.55
DYNAMIC (kgf)	1010
STATIC (kgf)	1730
LEAD/PITCH	16/4

ROUGH M/C	FIN M/C	GRD		MATERIAL	SHAFT:CF53/Equiv. NUT:SNM220/Equiv.
$\sqrt{Ra25}$	$\sqrt{Ra6.3}$	$\sqrt{Ra0.4}$		THREAD BALL TRACK	HRC 56~62
TOLERANCE mm					
UP	6	30	120	300	600
TO	6	30	120	300	600
					1200
					2400
					OVER
	± 0.1	± 0.2	± 0.3	± 0.4	± 0.5
					± 0.8
					± 1.0
					± 1.5
DATE	INITIALS	 HIWIN CORPORATION 12455 Jim Dhamer Dr, Huntley, IL 60142			
DRAWN	D.W				
CHECKED	T.C.				
MFG APPR.	A.H				
TITLE:		STANDARD STOCK BALLSCREW			
PART NUMBER:		4R15-16K3-FSCEW-XXXX-XXXX-0.05			
SIZE	DWG. NO.	REV	SCALE	NTS	
B	W-SBS-15-16-A01	N/C			

HIWIN CONFIDENTIAL