



PRELOAD(kgf)	~
R.D	-
S.F (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	12.3
BALL DIA.	2
BACKLASH Δ	0.03MAX
CIRCUIT	3
LEAD ANGLE	7.49
DYNAMIC (kgf)	277
STATIC (kgf)	492
LEAD/PITCH	5.08/2.54

SPEC: 2R12-5.08T3-DRSI

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA.
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH Δ
DN VALUE	EI TYPE ASSEMBLY METHOD	CIRCUIT
MAX. FEED RATE(m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE
ACCELERATION(m/se ²)	CUSTOMER MC TYPE	DYNAMIC (kgf)
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)
		LEAD/PITCH

UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R SCALE 1: X MA AL SH: RCLLED DATE 2007.07.16 NT: SNCM220/SCM415 DWG JIANET THREAD BALL TRACK APPD Michelle HRC 56 ~ 62 PROCESS NO. G CUSTR F-CHICAGO DWG.NO. A11505A4
--

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
 *未畫倒角者以R0.5MAX
 * THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

2007.07.16	MOD. Δ	MICHELLE
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.